

INCORPORATING
PRODUCTS AWARDED
THE QUEENS AWARD
FOR ENTERPRIZE;
INNOVATION
2009



THE QUEEN'S AWARDS
FOR ENTERPRIZE
INNOVATION
2009



ENVIRONMENTAL TECHNOLOGY

reliability-focused-solutions.com

Reliability
Focused
Solutions



LabTecta-PB™

PATENT PENDING in over 39 countries.




“Engineered for Misalignment”

LabTecta-PB™ - Plummer/Pillow block design

Until now, sealing split bearing blocks has always been an issue. Alignment between the shaft and bearing block can vary significantly. Existing labyrinth rings have large clearances in order to accommodate the angular misalignment but provide little protection against contamination.


Contact sealing solutions have very short lives because the misalignment overloads the sealing surfaces. The revolutionary AESSEAL® design for bearing blocks is specifically engineered to absorb the misalignment and maximize the performance of the seal. Major benefits are:

- Extended bearing and equipment life
- Better protection against bearing contamination
- Reduced lubrication requirements
- Better lubrication retention
- Reduced operating temperature




Misalignment? - No problem

The LabTecta-PB™ utilizes a unique two piece stator design that provides a self-aligning joint that allows the seal to align both to the bearing block and the shaft. The joint also provides constant pressure on the static elastomer to provide positive sealing throughout the range of motion.




The LabTecta-PB™ accepts the same degree of angular misalignment as ANY standard seal offered by the OEM.

LabTecta-PB™ - Designed to suit Plummer/Pillow block applications



Standard cross section

Dimensions may vary dependent upon size and model. If in doubt, contact the Bearing Protection Division.



Thin cross section design variant

Item	Description	Material
1	LabTecta™ Rotary	Phosphor Bronze
2	Outboard Rotor O Ring	Viton®
3	Arknian™ Shut Off Device	Compound Elastomer
4	Arknian™ Energizer	Viton®
5	Face Shield	Composite Material
6	Stator Housing	Phosphor Bronze
7	Stator Housing O Ring	Viton®
8	Inboard Rotor O Ring	Viton®
9	Adaptor	Phosphor Bronze
10	Adaptor O Ring	Viton®
11	Flexi-Ring	Oil Resistant Silicon

Pillow block dimensions are already available for the following models as of January 2008:

SKF® SNL	All housings
SKF® SAF	507, 510, 511, 513, 515, 516, 517, 518, 520, 522, 524, 526, 528, 530, 532, 534
FAG SNV	All housings

All other models will require dimensions prior to manufacture. Refer to back page for more information.



Pulp & Paper Industry, Canada. LabTecta-PB™ installed on a dryer roll (Case Ref: 3369)





Pulp & Paper Industry, Argentina. 70mm LabTecta-PB™ installed on a SKF® SNL 516-613 pillow block roll (Case Ref: 3217)




70mm LabTecta-PB™ with Air Purge installed on a centrifugal fan pillow block SKF® SNL 516-613 in Argentina (Case Ref: 3218)

Alternative Designs



Housing Dimensions



Application Data

Block Manufacturer:

Block Number:

Speed:

Bearing Type:

Shaft: Horizontal Vertical

Max. Axial Movement:

Max. Angular Misalignment:

Seal Material: Bronze Stainless Steel

Lubrication Type/System:

Other:

Complete the information above and send to:

UK Fax: +44 (0) 1709 720788 USA Fax: +1 865 531 0571 Email: sales@labtecta.com

Further information about the AESSEAL® LabTecta™ range is available in the standard LabTecta™ brochure. Email sales@labtecta.com to request a copy or download it from our website - www.labtecta.com

THIS DOCUMENT IS DESIGNED TO PROVIDE DIMENSIONAL INFORMATION AND AN INDICATION OF AVAILABILITY. FOR FURTHER INFORMATION AND SAFE OPERATING LIMITS CONTACT OUR TECHNICAL SPECIALISTS AT THE LOCATIONS BELOW.



USE DOUBLE MECHANICAL SEALS WITH HAZARDOUS PRODUCTS. ALWAYS TAKE SAFETY PRECAUTIONS:

- GUARD YOUR EQUIPMENT
- WEAR PROTECTIVE CLOTHING



UK Sales & Technical advice:
 AESSEAL plc
 Mill Close
 Templeborough
 Rotherham
 S60 1BZ
 United Kingdom

INVESTOR IN PEOPLE

Telephone: +44 (0) 1709 369966
 Fax: +44 (0) 1709 720788
 E-mail: seals@aessecal.com
 Internet: http://www.aessecal.com

Distributed by:

Our Purpose: *'To give our customers such exceptional service that they need never consider alternative sources of supply.'*

USA Sales & Technical advice:
 AESSEAL Inc.
 355 Dunavant Drive
 Rockford,
 TN. 37853
 USA

Telephone: +1 865 531 0192
 Fax: +1 865 531 0571
 E-mail: usa@aessecal.com

ALL SIZES ARE SUBJECT TO MANUFACTURING TOLERANCES. WE RESERVE THE RIGHT TO MODIFY SPECIFICATIONS AT ANY TIME.

AESSEAL plc recognise all trademarks and trademark names as the property of their owners. AESSEAL® is a Registered Trademark of AESSEAL plc. LabTecta™, LabTecta-PB™, MagTecta™ and MagTecta-PB™ are Trademarks of AESSEAL plc. SKF® is a Registered Trademark of SKF.